


## **ENERGIZER CR2025**



## **Industry Standard Dimensions**

mm (inches)



0.20 (0.008) Maximum Ref. Permissible deflection from a flat.


## **Simulated Application test**

Typical Performance at 21°C (70°F)

Schedule:	Typical Drains: at 2.9V	Load	Cutoff 2.0V
	(mA)	(ohms)	(hours)
Continuous	0.193	15,000	845

## **Typical Discharge Characteristics**

Load: 15K ohms - Continuous Typical Drain @ 2.9V: 0.193 mA



# Lithium Coin

## **Specifications**

Classification: "Lithium Coin"

Chemical System: Lithium / Manganese Dioxide (Li/MnO<sub>2</sub>)

Designation: ANSI / NEDA-5003LC, IEC-CR2025

Nominal Voltage: 3.0 Volts

**Typical Capacity:** 163 mAh (to 2.0 volts) (Rated at 15K ohms at 21°C)

Typical Weight: 2.6 grams (0.08 oz.)

**Typical Volume:** 0.8 cubic centimeters (0.05 cubic inch)

Max Rev Charge: 1 microampere

Energy Density: 176 milliwatt hr/g, 616 milliwatt hr/cc

Typical Li Content: 0.078 grams (0.0028 oz.)

UL Listed: MH12454

**Shipping:** For complete details, please reference: Global (except US): Special Provision A45 of the International


Air Transport Association Dangerous

Goods Regulations

United States: 49 CFR 173.185

**Safety** - lithium coin batteries lodged in the esophagus should be removed immediately. Leakage, chemical burns and potential perforation can occur within hours of ingestion. Seek medical attention immediately. Have physician call the NATIONAL BATTERY INGESTION HOTLINE for advice and follow-up (202)-625-3333) collect day or night.

### Cross Section



#### Internal Resistance Characteristics


Pulse Test at 21°C (70°F)

**Bkgnd Drain:** Continuous

15K ohms 0.193 mA @2.9V

Pulse Drain: 2 seconds X 12 times/day

400 ohms 6.8 mA @2.7V



### **Important Notice**

This datasheet contains typical information specific to products manufactured at the time of its publication.

© Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

Form No. EBC - 4119J Page 1 of 1